Product datasheet

Specifications





Elbow, Canalis KSA250, aluminium, 100/160/250A, fixed dimensions (A/B 250mm), to go upward, 3L+N+PE, white RAL9001

KSA250DLE401

Main

mann		
Range Of Product	Canalis	
Product Name	KS	
Device Short Name	KSA	
Offer Type	Classic	
Product Or Component Type	Elbow	
Busbar Description	Description Standard	
Product Compatibility	Canalis KSA busbar trunking 100250 A	
Device Application	Change direction	
Conductors Material	ors Material Aluminium	
Busbar Trunking Polarity	3L + N + PE	
[le] Rated Operational Current	250 A at 35 °C	
Ip Degree Of Protection	IP55 conforming to IEC 60529	
[Ue] Rated Operational Voltage	230690 V	
Network Frequency	requency 50/60 Hz	
Operating Angle	90 °	
Direction Change Type	direction 1: edgewise to upward -	
Colour	White (RAL 9001)	
Dimension Type	Fix	

Complementary

Length	250 mm for side A 250 mm for side B	
Width	54 mm	
Height	146 mm	
Net Weight	2.6 kg	
Mounting Location	On trunking	
Mounting Position	Any position	
Electrical Connection	Lubricated sliding contact	
Mounting Mode	By screws	
Standards	IEC 61439-1 IEC 61439-6	

Environment

Ik Degree Of Protection IK08 conforming to IEC 62262

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	35.0 cm
Package 1 Length	36.5 cm
Package 1 Weight	4.95 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	7
Package 2 Height	52.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Backage 2 Weight	29.0 kg

Package 2 Weight

38.0 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Dimensions



