# **Product datasheet**

Specifications





Elbow, Canalis KSA250, Alu, 100/160/250A, sides A/B made to measure, to go downward, special angle, 3L+N+PE, RAL9001

KSA250DLF43B

#### Main

Range Of Product	Canalis	
Product Name	KS	
Device Short Name	KSA	
Offer Type	Advanced	
Product Or Component Type	Elbow	
Busbar Description	Standard on made to measure (per side)	
Product Compatibility	luct Compatibility Canalis KSA busbar trunking 400 A	
Device Application	Change direction	
Conductors Material	Aluminium	
Busbar Trunking Polarity	3L + N + PE	
[le] Rated Operational Current	250 A at 35 °C	
Ip Degree Of Protection	IP55 conforming to IEC 60529	
[Ue] Rated Operational Voltage	230690 V	
Network Frequency	50/60 Hz	
Operating Angle	95175 °	
Direction Change Type	Change Type direction 1: edgewise to downward - neutral to right	
Colour	White (RAL 9001)	
Dimension Type	Made to measure	

### Complementary

•	•	
Length	250750 mm for side A 250750 mm for side B	
Width	54 mm	
Height	146 mm	
Mounting Location	On trunking	
Mounting Position	Any position	
Electrical Connection	Lubricated sliding contact	
Mounting Mode	By screws	
Standards	IEC 61439-1 IEC 61439-6	

#### **Environment**

II. Danna Of Bustastian	11/00 / 11/10/00/00
Ik Degree Of Protection	IK08 conforming to IEC 62262

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	87.0 cm
Package 1 Length	87.0 cm
Package 1 Weight	34.0 ka



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Reach Free Of Svhc	
	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations