Product datasheet

Specification





circuit breaker EasyPact CVS100B, 25kA at 415VAC, 32A TMD trip unit, 4P 3d

LV510312

Main

Range	EasyPact
Product Name	EasyPact CVS
Device Short Name	CVS100B
Product Or Component Type	Circuit breaker
Device Application	Distribution
Poles Description	4P
Protected Poles Description	3D
Earth Leakage Protection (Vigi Add On)	Without
[In] Rated Current	32 A at 40 °C
Network Type	AC
Utilisation Category	Category A
[Icu] Breaking Capacity	40 kA lcu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA lcu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA lcu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Rating	32 A at 40 °C
Protection Type	Overload protection (thermal) Short-circuit protection (magnetic)

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to EN/IEC 60947-2
Network Frequency	50/60 Hz
Breaking Capacity Code	В
[Ics] Rated Service Breaking Capacity	15 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Neutral Position	Left
Mechanical Durability	30000 cycles
Electrical Durability	12000 cycles 415 V In conforming to IEC 60947-2
Control Type	Toggle
Thermal Protection Adjustment Range	22.432 A
Neutral Protection Setting	No protection (3D)

19 Apr 2024 Life Is On Schneider

Long Time Pick-Up Adjustment Type Ir	Adjustable
Long Time Pick-Up Adjustment Range	0.71 x ln
Long Time Delay Adjustment Type	Fixed
Instantaneous Pick-Up Adjustment Type Ii	Fixed
Instantaneous Pick-Up Adjustment Range	400 A
Contact Position Indicator	Yes
Mounting Mode	Fixed
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connections - Terminals	Screw connection
Connection Pitch	35 mm
Compatibility Code	CVS100
Width	140 mm
Depth	86 mm
Height	161 mm
Net Weight	1.9 kg

Environment

Standards	EN 60947-2 IEC 60947-2							
Product Certifications	IEC GOST							
Electrical Shock Protection Class	Class II							
Pollution Degree	3 conforming to IEC 60664-1							
Ip Degree Of Protection	IP40							
Ambient Air Temperature For Operation	-2570 °C							
Ambient Air Temperature For Storage	-5085 °C							

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.000 cm
Package 1 Width	15.000 cm
Package 1 Length	19.200 cm
Package 1 Weight	2.236 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	9
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm

Package 2 Weight 20.500 kg

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

19 Apr 2024

LV510312


Dimensions Drawings





Туре	Α	A1	A2	A3	A4	A/5	A6	A7	A8	A9	В	B1	B2	C1	C2	C3	E1
CV9100H60/250	66.5	161	64	146	179.5	155.5	226	169	226	250,5	52.5	105	446	81	66	191@	62.5
C245/400/930	127.5	296	142.原	200	297	227.5	355	242.5	300	337	70	140	188	95.5	110	163	100
Type	E2	E3	E4	E5	E6	E7	EB	F1	F2	F3	G1	G2	G3	G4	G5	ØT	U
CM2100M60/250	125	ন্ত্র	14D	137.5	200	145	215	216	17.5	70	26	78	13.5	25	17.5	24	y 32
CV5400/630	200	113.5	227	200	200	2135	327	45	22.5	90	-	000	-	-		32	y 35


[2] CJ-126mm for EasyPast CVS2509JF.

Assembly









Туре	Α	A1	A2	A3	A4	A/5	A6	A7	A8	A9	В	B1	B2	C1	C2	C3	E1
CW8100160/250	66.5	161	64	146	179.5	155.5	236	169	226	250.5	52.5	105	146	81	06	1110	62.5
C245400/930	127.5	296	142,5	200	297	227.5	355	242.5	3.00	337	70	140	188	95.5	110	168	100
Type	E2	E3	E4	E5	E6	E7	EB	F1	F2	F3	G1	G2	G3	G4	G5	ØT	U
CM2100M60/250	125	FE	140	137.5	200	145	215	216	17.5	70	56	78	12.5	25	17.5	24	y 32
CV5460/830	200	113.5	227	200	300	213.5	327	45	22.5	90	-	000	-	-	-	32	y 35

[8] CJ-126mm for EasyPast CVS250fuF.

Performance Curves

