


Product datasheet

Specifications



PLS box, polyester rear, opaque PC cover IP65 36x72x23cm

NSYPLSC3672A

 **Discontinued on:** 31 Oct 2016

 **Discontinued**

Main

Range	Thalassa
Product Name	Thalassa PLS
Device Short Name	PLS
Enclosure Type	Multi-purpose
Category	Insulating modular box
Nominal Height	360 mm
Nominal Width	720 mm
Nominal Depth	230 mm
Enclosure Mounting	Wall mounted
Device Composition	1 cover: on enclosure 1 rear part: on enclosure locking screws
Body Type	One piece moulded
Type Of Front Cover	High plain cover
Lock Type	Slot screw

Complementary

Removable Parts	Cover locking screw
Material	Cover: polycarbonate Rear: polyester reinforced with fibreglass
Colour	Body: grey (RAL 7032)
Standards	IEC 62208 NEMA 4X NEMA classification 13
Product Certifications	UL

Environment

Electrical Insulation Class	Class II
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to IEC 62262
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-30...120 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------