

Product datasheet

Specifications



Thalassa, PC box IP66 IK08
RAL7035 Int.H150W105D80
Ext.H164W121D87 opaque PC
cover H20

NSYTBP16128

Main

| | |
|---------------------|--|
| Range | Thalassa |
| Product Name | Thalassa TBP |
| Device Application | Multi-purpose |
| Category | Industrial box |
| Height | 164 mm |
| Width | 121 mm |
| Depth | 87 mm |
| Internal Height | 150 mm |
| Internal Width | 105 mm |
| Internal Depth | 80 mm |
| Enclosure Mounting | Wall mounted |
| Device Composition | 1 body 1 cover 4 cover screw |
| Quantity Per Set | Set of 2 |
| Body Type | One piece moulded |
| Type Of Front Cover | Low plain cover |
| Cover Fixing | Plastic screws |
| Lock Type | Captive screw flat outside sealed area |
| Removable Parts | Cover by captive screws |

Complementary

| | |
|-----------------------------|---|
| Material | Polycarbonate |
| Colour | Grey (RAL 7035) |
| Standards | UL 508 A IEC 62208 |
| Product Certifications | TÜV UL |
| Electrical Insulation Class | Class II |
| Mounting Location | Outdoor (with canopy or shelter and anticondensation valve) |
| Net Weight | 0.33 kg |

Environment

| | |
|--|------------------------------|
| Ip Degree Of Protection | IP66 conforming to NEMA 4.4X |
| Ik Degree Of Protection | IK08 conforming to IEC 62262 |
| Fire Resistance | 960 °C |
| Ambient Air Temperature For Storage | -15...60 °C |
| Operating Temperature | -25...80 °C |

Packing Units

| | |
|-------------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.7 cm |
| Package 1 Width | 12.1 cm |
| Package 1 Length | 16.4 cm |
| Package 1 Weight | 330 g |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 384 |
| Package 2 Height | 120 cm |
| Package 2 Width | 80 cm |
| Package 2 Length | 136 cm |
| Package 2 Weight | 160 kg |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty | 18 months |
|-----------------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)
