Product datasheet

Specifications





Harmony XVR, Illuminated beacon without buzzer, blue, 100mm, integral LED, 12...24V DC

XVR3B06

Main

Range Of Product	Harmony XVR
Product Or Component Type	Beacon
Device Short Name	XVR3
Beacon Or Indicator Bank Unit Type	LED unit
Mounting Diameter	100 mm
Light Source	LED, blue
Device Application	Forklift Bulldozer Automated guided vehicle (AGV)

Complementary

Signalling Type	Flashing Blinking Rotating	
Assembly Style	Ready assembled	
Material	PC (polycarbonate): lenses PBT (polybutylene terephthalate) + PC (polycarbonate): body EPDM (ethylene propylene diene monomer): base	
[Us] Rated Supply Voltage	1224 V DC	
[Ue] Rated Operational Voltage	1030 V DC	
Inrush Current	3 A	
Power Consumption In W	2.8 W	
Marking	CE	
Installation Direction	Upright indoor Sideways indoor Inverted indoor Upright outdoor	
Electrical Insulation Class	Class II	
Current Consumption	3000 mA	
Length	100 mm	
Width	100 mm	
Height	139 mm	
Net Weight	0.484 kg	

Environment

nbient Air Temperature For	-2050 °C
ation	

Ambient Air Temperature For Storage	-3570 °C
Relative Humidity	3585 % without condensation
Vibration Resistance	4.6 gn (sideways) 4.6 gn (inverted) 7.1 gn (upright)
Ip Degree Of Protection	IP65 (upright) IP23 (sideways) IP23 (inverted)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	14.3 cm
Package 1 Length	13.8 cm
Package 1 Weight	3.68 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	29.44 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

XVR3B06

Dimensions Drawings


Dimensions




Mounting and Clearance

Panel Cut-out

Straight wiring




Side wiring



XVR3B06

Connections and Schema

Wiring Diagram



- (1) Black
- (2) White
- (3) Fuse(Rated Current>2A)