

Product datasheet

Specifications



Multisound siren, Harmony XVS,
prewired, white colour, 0...105dB,
43tones, 12...24V DC

XVS14BMW

Main

Range Of Product	Harmony XVS
Product Or Component Type	Multisound siren
Device Short Name	XVS

Complementary

Colour	White
Material	ASA (Acrylonitrile Styrene Acrylate): front ASA (Acrylonitrile Styrene Acrylate): back PC (polycarbonate): back cover
Net Weight	1 kg
Marking	CE
Mounting Support	Bracket
Fixing Mode	3 holes Ø 9 mm
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	350 mA at 24 V 250 mA at 12 V
Electrical Connection	Cable: 6.5...8.5 mm, 0.33 mm² / AWG 22 (signalling circuit) Cable: 6.5...8.5 mm, 0.52 mm² / AWG 20 (power circuit)
Width	140 mm
Height	114 mm
Depth	223 mm

Environment

Signalling Type	43 tones siren
Standards	IEC 61000-6-2 EN 55014-2 EN 55022 IEC 61000-6-3
Product Certifications	UL
Protective Treatment	TC
Ambient Air Temperature For Storage	-35...70 °C
Ambient Air Temperature For Operation	-10...50 °C
Overvoltage Category	Class II conforming to IEC 61140
Ip Degree Of Protection	IP53 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Us] Rated Supply Voltage	12 V DC
	24 V DC
Noise Level	0...105 dB (continuous or intermittent tone) at 1 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30 cm
Package 1 Width	18 cm
Package 1 Length	18.5 cm
Package 1 Weight	1.307 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	9.094 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	24
Package 3 Height	60 cm
Package 3 Width	80 cm
Package 3 Length	24 cm
Package 3 Weight	33.024 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-------------------	--

China Rohs Regulation	China RoHS declaration
-----------------------	--

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---

Dimensions Drawings

Siren

Dimensions

