

Folha de dados do produto

Especificações



EcoStruxure Operator Terminal Expert Professional licença única digital

HMIPELCZLSPAZZ

Principal

Linha De Produto	EcoStruxure especialista em terminal de operador
Tipo De Produto Ou Componente	Licença
Formato	Digital
Tipo De Software	Professional
Tipo De Licença	Node locked license
Variante	Tempo de construção
Versão Do Software	V3.5
Operating System Requirement	Windows 10 32 bit
Requerimentos Do Sistema	8 GB DE RAM 30 GB de espaço no disco rígido
Idioma	Inglês Italiano Chinês Espanhol Francês Alemão Português Coreano

Complementar

License Category	Permanent
------------------	-----------

Isenção de responsabilidade Esta documentação não tem como objetivo substituir nem deveser utilizada para determinar a adequação ou confiabilidade desses produtos para aplicações específicas

Protocolo Da Porta De Comunicação	CANopen escravo Couzet Automation millenium 3 FBD Emerson Industrial Automation mestre Modbus SIO Control Techniques mestre Modbus SIO Emerson Process Management ROC Além disso Ethernet Emerson Process Management ROC SIO HTTP IPsec Mitsubishi A series Ethernet Mitsubishi série FX CPU direta Mitsubishi FX série Ethernet Mitsubishi iQ-R/F series Ethernet SLMP client Mitsubishi Q série CPU direta Mitsubishi série Q QnU CPU Ethernet Mitsubishi Q / QnA série série Modbus Organization Modbus SIO mestre ASCII Modbus Organization mestre Modbus SIO Modbus Organization Modbus SIO escravo Modbus Organization Modbus TCP mestre Modbus Organization escravo Modbus TCP Omron CS/CJ/CP series host link Omron CS/CJ/CP/NX series Ethernet Omron CS/CJ/NJ/NX series Ethernet/IP OPC UA server Profibus DP slave Rockwell Automation Ethernet/IP Rockwell Automation DF1 Rockwell Automation DH485 Schneider Electric mestre Modbus SIO Schneider Electric Modbus TCP mestre Schneider Electric Modbus TCP mestre via USB Schneider Electric Machine expert network Schneider Electric PacDrive Schneider Electric Uni-Telway Schneider Electric Zelio Logic Siemens Simatic S7 Ethernet Siemens Simatic S7 MPI direta Siemens TIA portal Ethernet websocket
Versão De Software Anterior	V3.4
Função De Software	Professional screen design Simulation Alarms and events Blocky script Convertors Dockable windows interface environment Export with CSV and tab delimiter Import with CSV and tab format Data and operation logging Multi language development Multi language tables Object binding and properties Target binding and properties Project transfer (Ethernet, filesystem, USB cable) Recipes Screens (contents and folders) Security (levels, project, users) Project and application settings System keypad Text script Color themes Variable (arrays, binding, properties, structures) Online and integrated help system Servidor OPC UA Web server API
Compatibilidade De Gama	Harmony GTU Harmony GTUX Harmony ST6 Harmony STM6 Harmony STO7 Harmony iPC
Hosting Option	On-premise
License Size	Single (1 station)

Processor Requirement	Intel core i3 8th generation
	Intel core i5 8th generation
Resolução De Exibição	1280 x 720 pixels HD

Garantia contratual

Garantia	18 meses
----------	----------