Product data sheet

Specifications





distributed analog output Modicon Momentum - 4 Output - 4..20 mA

170AAO92100

Main

Range Of Product	Modicon Momentum automation platform
Product Or Component Type	Analogue output base
Complementary	
Analogue Output Number	4
Data Format	Full 16 bits signed
Analogue Output Range	+/- 10 V 12 bits + sign >= 1 kOhm 420 mA 12 bits + sign <= 0.6 kOhm
Maximum Load Capacitance	1 µF
Absolute Accuracy Error	+/- 0.2 % of full scale +/- 10 V 77 °F (25 °C) +/- 0.25 % full scale +/- 10 V 140 °F (60 °C) +/- 0.4 % of full scale 420 mA 77 °F (25 °C) +/- 0.5 % of full scale 420 mA 140 °F (60 °C)
Temperature Drift	10 %oFS/°C +/- 10 V 140 °F (60 °C) 30 %oFS/°C 420 mA 140 °F (60 °C)
Update Time	2 ms
Full Scale	10 V +/- 10 V 2 mA 420 mA
Fail State	Hold Reset to full scale Reset to zero
Isolation Between Channels And Ground	500 V AC for 1 minute
Maximum Power Dissipation In W	8.5 W
Protection Type	Internal 2 A slow-blow
Output Short-Circuit Protection	With in voltage circuit
External Power Requirement	+/- 30 V DC 24 V DC
Permissible Common Mode Voltage	250 V 4763 Hz AC between channels to ground 250 V 4763 Hz DC
Reverse Polarity Protection	Internal
Marking	CE
Local Signalling	Channel status 4 LEDs
Current Consumption	150 mA 24 V DC actuator 530 mA 24 V DC base
Module Format	Standard
Height	4.92 in (125 mm)

Depth	1.87 in (47.5 mm)
Width	5.57 in (141.5 mm)
Net Weight	0.47 lb(US) (0.215 kg)

Environment

Product Certifications	UL CSA
Protective Treatment	TC
Resistance To Electrostatic Discharge	4 kV contact IEC 801-2 8 kV on air IEC 801-2
Resistance To Electromagnetic Fields	9.14 V/yd (10 V/m) 801000 MHz IEC 801-3
Ambient Air Temperature For Operation	32140 °F (060 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	10.24 in (26.0 cm)
Package 1 Weight	13.23 oz (375.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	8.27 lb(US) (3.75 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	80
Package 3 Height	29.53 in (75.0 cm)
Package 3 Width	15.75 in (40.0 cm)
Package 3 Length	31.50 in (80.0 cm)
Package 3 Weight	99.21 lb(US) (45 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings


Standard Adapter on a Typical Base

Dimensions




Mounting and Clearance

Mounting on a Wall



Connections and Schema

External Wiring Diagram



Internal Pin Connections

