

Product data sheet

Specifications



NEMA Contactor, Type S, nonreversing, Size 00, 9A, 3 HP at 550 VAC, 3 phase, up to 100 kA, 3 pole, 600 VAC coil, NEMA 1

8502SAG12V07

Main

| | |
|----------------|---------------|
| Product Type | Contactor |
| Product Range | 8502S |
| Contactor Type | Non-reversing |

Complementary

| | |
|------------------------|--|
| Nema Size | 00 |
| Rated Current | 9 A |
| Number Of Poles | 3P |
| Maximum Voltage Rating | 600 V AC |
| Phase | 3 phases |
| Horsepower Rating | 1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC |
| Scrr | Circuit-breaker 70 A maximum, SCCR: 100 kA at 480 V AC Fuse J 60 A maximum, SCCR: 100 kA at 600 V AC Fuse T 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK1 60 A maximum, SCCR: 100 kA at 600 V AC Fuse RK5 60 A maximum, SCCR: 100 kA at 600 V AC |
| Coil Voltage | 600 V AC 60 Hz 550 V AC 50 Hz |
| Control Circuit Type | Common control circuit |
| Control Units | No control units |
| Pilot Light | No indicator |
| Auxiliary Contacts | Without |
| Other Equipment | Fuse not supplied |
| Terminal Type | Screw clamp terminals |
| Height | 10.00 in (254 mm) |
| Width | 5.98 in (152 mm) |
| Depth | 5.28 in (134 mm) |

Environmental

| | |
|----------------|---------------------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | UL listed file E78351 CCN NLDX CSA |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|