

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 2, 3-Pole, Motor Logic SSOLR (Class 20), NEMA 12

8536SDA1V81CF4H20P1P2T

### Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

### Complementary

Nema Size	2
Rated Current	45 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phases
Type Of Overload	Solid state Motor Logic class 20
Horsepower Rating	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
Coil Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Control Circuit Type	Control circuit transformer
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent Green indicator off incandescent
Other Equipment	2 fuses (primary)
Terminal Type	Screw clamp terminals

### Environment

Enclosure Type	NEMA 12 painted sheet steel
Certifications	UL listed NEMA CSA

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications