

# Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,  
60 A, 3 pole, NEMA 1, 208-120V  
60Hz

8903SPG2V84CF4P1TX22

## Main

Product	Electrically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	208 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	60 A
Number Of Poles	3P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	2 NO + 2 NC
Control Circuit Fusing	2 fuses primary circuit
Other Options	None
Electrical Connection	Lugs
Height	14.13 in (359 mm)
Depth	7.56 in (192 mm)
Width	14.88 in (378 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL listed CSA

## Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications