


Product data sheet

Specifications

Cover for cable duct - Width=30mm

AK2CA3



Main

| | |
|------------------------------------|--|
| Product Or Component Type | Cover |
| Accessory / Separate Part Category | Cabling accessories |
| Range Compatibility | Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM |
| Mounting Support | Cable duct 1.18 in (30 mm) |
| Quantity Per Set | Set of 8 |

Complementary

| | |
|------------|--------------------------|
| Colour | Blue RAL 5000) |
| Length | 78.74 in (2000 mm) |
| Width | 1.18 in (30 mm) |
| Material | PVC (polyvinyl chloride) |
| Net Weight | 0.44 lb(US) (0.2 kg) |

Environment

| | |
|---------------------------------------|-----------------------------------|
| Ambient Air Temperature For Operation | 23...140 °F (-5...60 °C) |
| Flame Retardance | V-0 UL 94 |
| Fire Resistance | 1760 °F (960 °C) IEC 60695-2-1/1 |
| Standards | VDE 0660 VDE 0506 DIN 43659 |

Packing Units

| | |
|------------------------------|---------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.18 in (3 cm) |
| Package 1 Width | 3.94 in (10 cm) |
| Package 1 Length | 78.74 in (200 cm) |
| Package 1 Weight | 8.54 oz (242 g) |
| Unit Type Of Package 2 | CAR |
| Number Of Units In Package 2 | 8 |
| Package 2 Height | 79.72 in (202.5 cm) |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-------------------------|
| Package 2 Width | 2.76 in (7 cm) |
| Package 2 Length | 2.36 in (6 cm) |
| Package 2 Weight | 4.37 lb(US) (1.982 kg) |
| Unit Type Of Package 3 | PAL |
| Number Of Units In Package 3 | 1792 |
| Package 3 Height | 39.76 in (101 cm) |
| Package 3 Width | 79.72 in (202.5 cm) |
| Package 3 Length | 47.24 in (120 cm) |
| Package 3 Weight | 1047.20 lb(US) (475 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | | |
|---|----------------------------|---|
|  | Reach Free Of Svhc | |
|  | Toxic Heavy Metal Free | |
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | | REACH Declaration |
| | | |
| Eu Rohs Directive | | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| | | |
| China Rohs Regulation | | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |