Product data sheet

Specifications





Busbar, Linergy HK, 160A, 4 conductors, L452mm, for mounting in enclosure W800mm

AK5JB144

Main

Range	Linergy
Product Name	нк
Product Or Component Type	Busbar
Device Application	Distribution
Tap-Offs (18 Mm)	18
Bar Length	17.80 in (452 mm)
Enclosure/Cubicle Width	800 mm
Network Type	AC
[le] Rated Operational Current	160 A 95 °F (35 °C)
[Ue] Rated Operational Voltage	400 V off-load plugging-in and unplugging, with supply switched on)IEC 60439-1 480 V off-load plugging-in and unplugging, with supply switched on)CSA 480 V off-load plugging-in and unplugging, with supply switched on)UL 600 V plugging-in and unplugging, with supply switched off)CSA 600 V plugging-in and unplugging, with supply switched off)UL 690 V plugging-in and unplugging, with supply switched off)IEC
Number Of Conductors	4

Complementary

Bar Width	1.77 in (45 mm)
Width	3.19 in (81 mm)
Depth	3.23 in (82 mm)
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak Current	25 kA
I ² T On Activation	1000000 A ² .s
Protection Type	AM fuses In = 160 A, Isc = 100 kA, Ie = 160 A GF fuses In = 160 A, Isc = 100 kA, Ie = 160 A NS160H circuit breaker In = 160 A, Isc = 36 kA, Ie = 160 A NS160H circuit breaker In = 160 A, Isc = 70 kA, Ie = 160 A
Connections - Terminals	Connector 0.000.11 in ² (2.570 mm ²) flexible with cable end Connector 0.000.11 in ² (2.570 mm ²) rigid
Tightening Torque	88.51 lbf.in (10 N.m)
Mounting Position	Vertical using side stop AK5BT01 on mounting plates AK5PA Horizontal
Flame Retardance	V0 UL 94

Net Weight

Environment

Standards	IEC 60439 UL CSA DNV LROS (Lloyds register of shipping)	
Product Certifications		
Ip Degree Of Protection	IPxx B IEC 60529	
Fire Resistance	1562 °F (850 °C) IEC 60695	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.33 in (11.000 cm)
Package 1 Width	4.33 in (11.000 cm)
Package 1 Length	20.67 in (52.500 cm)
Package 1 Weight	2.52 lb(US) (1.143 kg)
Unit Type Of Package 2	P06
Number Of Units In Package 2	30
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	23.62 in (60.000 cm)
Package 2 Length	31.50 in (80.000 cm)
Package 2 Weight	104.26 lb(US) (47.290 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations