

Product data sheet

Specifications

Schneider Electric CHOM125CP

Picture

ⓘ Discontinued

HOMELINE CIRCUIT BREAKER 120V 25A 1P

CHOM125CP

ⓘ Discontinued on: Jan 26, 2021

Main

| | |
|--------------------------------|-------------------------------|
| Range Of Product | Homeline |
| Product Or Component Type | Miniature circuit-breaker |
| [In] Rated Current | 25 A |
| [Ue] Rated Operational Voltage | 120/240 V AC |
| Mounting Mode | Plug-on |
| Poles Description | 1P |
| Short-Circuit Current | 10 kA |
| Circuit Breaker Type | Standard |
| Circuit Breaker Application | HACR and Switching Duty rated |
| Electrical Connection | Screw clamp terminals |

Complementary

| | |
|---------------------------|--------------------------------|
| Number Of Spaces Required | 1 |
| Awg Gauge | AWG 14...AWG 8 aluminum/copper |

Environment

| | |
|---------------------------------------|----------------|
| Product Certifications | CSA |
| Ambient Air Temperature For Operation | 104 °F (40 °C) |

Packing Units

| | |
|------------------------------|---------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.00 in (7.62 cm) |
| Package 1 Width | 3.00 in (7.62 cm) |
| Package 1 Length | 1.00 in (2.54 cm) |
| Package 1 Weight | 5.28 oz (149.686 g) |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

| | | |
|-----------------------|----------------------------|---|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| | | |
| Eu Rohs Directive | | Compliant EU RoHS Declaration |
| | | |
| China Rohs Regulation | | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |