

Specifications



Mini circuit breaker, Homeline, 40A,
2 pole, 120/240VAC, 10kA AIR,
standard type, plug in, UL

CHOM240

Range Of Product	Homeline
Product Or Component Type	Miniature circuit-breaker
[In] Rated Current	40 A
[Ue] Rated Operational Voltage	120/240 V AC
Mounting Mode	Plug-on
Poles Description	2P
Short-Circuit Current	10 kA
Circuit Breaker Type	Standard
Circuit Breaker Application	HACR rated
Electrical Connection	Screw clamp terminals

Number Of Spaces Required	2
Awg Gauge	AWG 8...AWG 2 aluminum/copper

Product Certifications	CSA
Ambient Air Temperature For Operation	104 °F (40 °C)

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	11.20 oz (317.515 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	10.60 in (26.924 cm)
Package 2 Width	7.00 in (17.78 cm)
Package 2 Length	16.50 in (41.91 cm)
Package 2 Weight	36.86 lb(US) (16.719 kg)

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)