# **Product data sheet**

Specifications





Mini circuit breaker, Homeline, 50A, 2 pole, 120/240VAC, 10kA AIR, ground fault class A, plug in, UL

CHOM250GFI

#### Main

Range Of Product	Homeline
Product Or Component Type	Miniature circuit-breaker
[In] Rated Current	50 A
[Ue] Rated Operational Voltage	120/240 V AC
Mounting Mode	Plug-on
Poles Description	2P
Short-Circuit Current	10 kA
Circuit Breaker Type	Ground fault protecting class A 5 mA
Circuit Breaker Application	HACR rated
Electrical Connection	Screw clamp terminals

## Complementary

Number Of Spaces Required	2
Awg Gauge	AWG 12AWG 4 aluminum/copper

#### **Environment**

Product Certifications	CSA
Ambient Air Temperature For Operation	104 °F (40 °C)

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.60 in (9.144 cm)
Package 1 Width	5.40 in (13.716 cm)
Package 1 Length	2.20 in (5.588 cm)
Package 1 Weight	19.36 oz (548.847 g)



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information