

# Product data sheet

Specifications

SQUARE D



Safety switch, heavy duty, non fusible, 200A, 600V, 3 poles, 150hp, NEMA 4, 4X, 5, 304 steel, volt indicator, interlock 2

CHU364DSEI2J1WW

Discontinued

Discontinued on: Jul 4, 2023

End-of-service on: Aug 5, 2023

## Main

|                              |                                                                                                                                                                                                                                                                                                                                                               |
|------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range                        | Square D                                                                                                                                                                                                                                                                                                                                                      |
| Product                      | Single Throw Safety Switch                                                                                                                                                                                                                                                                                                                                    |
| Current Rating               | 200 A                                                                                                                                                                                                                                                                                                                                                         |
| Enclosure Rating             | NEMA 4/4X stainless steel 304                                                                                                                                                                                                                                                                                                                                 |
| Horsepower Rating            | 15 hp at 240 V AC 50...60 Hz for 1 phase motors<br>60 hp at 240 V AC 50...60 Hz for 3 phases motors<br>50 hp at 480 V AC 50...60 Hz for 1 phase motors<br>125 hp at 480 V AC 50...60 Hz for 3 phases motors<br>50 hp at 600 V AC 50...60 Hz for 1 phase motors<br>150 hp at 600 V AC 50...60 Hz for 3 phases motors<br>40 hp at 250 V DC<br>50 hp at 600 V DC |
| Disconnect Type              | Non-fusible disconnect                                                                                                                                                                                                                                                                                                                                        |
| Short Circuit Current Rating | 10 kA                                                                                                                                                                                                                                                                                                                                                         |
| Mounting Type                | Surface                                                                                                                                                                                                                                                                                                                                                       |
| Number Of Poles              | 3                                                                                                                                                                                                                                                                                                                                                             |
| Phase                        | 3 phases                                                                                                                                                                                                                                                                                                                                                      |
| Certifications               | CSA                                                                                                                                                                                                                                                                                                                                                           |
| Voltage Rating               | 600 V AC/DC                                                                                                                                                                                                                                                                                                                                                   |
| Wire Configuration           | 4-wire                                                                                                                                                                                                                                                                                                                                                        |
| Wire Size                    | AWG 6...250 kcmil copper or aluminum                                                                                                                                                                                                                                                                                                                          |

## Complementary

|                   |                                                                                                      |
|-------------------|------------------------------------------------------------------------------------------------------|
| Tightening Torque | 275 lbf.in (31.07 N.m) 0.02...0.20 in <sup>2</sup> (13.30...127 mm <sup>2</sup> ) AWG 6...250 kcmil) |
| Width             | 19.25 in (488.95 mm)                                                                                 |
| Height            | 29 in (736.60 mm)                                                                                    |
| Depth             | 8.88 in (225.55 mm)                                                                                  |

## Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications