

Product data sheet

Specifications

SQUARE D



Safety switch, heavy duty, non fusible, 200A, 600V, 3 poles, 150hp, NEMA 4, 4X, 5, 304 steel, volt indicator, interlock 2

CHU364DSEI2J2WW

Discontinued

Discontinued on: Jul 4, 2023

End-of-service on: Aug 5, 2023

Main

Range	Square D
Product	Single Throw Safety Switch
Current Rating	200 A
Enclosure Rating	NEMA 4/4X stainless steel 304
Horsepower Rating	15 hp at 240 V AC 50...60 Hz for 1 phase motors 60 hp at 240 V AC 50...60 Hz for 3 phases motors 50 hp at 480 V AC 50...60 Hz for 1 phase motors 125 hp at 480 V AC 50...60 Hz for 3 phases motors 50 hp at 600 V AC 50...60 Hz for 1 phase motors 150 hp at 600 V AC 50...60 Hz for 3 phases motors 40 hp at 250 V DC 50 hp at 600 V DC
Disconnect Type	Non-fusible disconnect
Short Circuit Current Rating	10 kA
Mounting Type	Surface
Number Of Poles	3
Phase	3 phases
Certifications	CSA
Voltage Rating	600 V AC/DC
Wire Configuration	4-wire
Wire Size	AWG 6...250 kcmil copper or aluminum

Complementary

Tightening Torque	275 lbf.in (31.07 N.m) 0.02...0.20 in ² (13.30...127 mm ²) AWG 6...250 kcmil)
Width	19.25 in (488.95 mm)
Height	29 in (736.60 mm)
Depth	8.88 in (225.55 mm)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications