


Product data sheet

Specifications



Loadcentre, QO, 1 phase, 12 spaces, 24 circuits, 70A main breaker, PoN, NEMA1, combo cover, CSA

CQO112M70PC

Main

Marketing Trade Name	QO
Product Type	Loadcentre
Cover Type	Combination flush/surface cover

Complementary

Tightening Torque	Cover 20 lb.in
Load Center Type	PoN Convertible Mains (breaker)
Rated Current	70 A
Number Of Spaces	12
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	24
Number Of Phases	1 phase
Voltage Rating	240 V AC
Height	14.92 in (379 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	CSA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.70 in (14.478 cm)
Package 1 Width	16.00 in (40.64 cm)
Package 1 Length	17.50 in (44.45 cm)
Package 1 Weight	17.60 lb(US) (7.983 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)