

Product data sheet

Specifications



Mini circuit breaker, E-Frame, 25A, 1 pole, 277 VAC, 25 kA max, bolt on

EDB14025

Main

Range Of Product	125 A Frame EDB-EGB-EJB
Product Or Component Type	Miniature circuit-breaker
Device Short Name	EDB
Module Type	E-Frame
Trip Unit Rating	875 A

Complementary

[In] Rated Current	25 A
Maximum Operating Voltage	277 V AC
Awg Gauge	AWG 12...AWG 6 aluminum AWG 14...AWG 6 copper
Breaking Capacity	18 kA 277 V AC 18 kA 240 V AC 25 kA 120 V AC 18 kA 120/240 V AC
Circuit Breaker Application	HID rated HACR rated
Electrical Connection	Lugs aluminum
Holding Current	270 A
Local Signalling	Trip indicator
Mounting Mode	Bolt-on
Number Of Poles	1
Number Of Spaces	1
Number Of Spaces Required	1
Product Destination	NF panelboard
Protection Type	Overload Short-circuit
Trip Unit Technology	Thermal-magnetic
Breaking Capacity Code	D
Tightening Torque	30.09 lbf.in (3.4 N.m) 0.00...0.02 in² (2.5...16 mm²) AWG 14...AWG 6)
Height	5.66 in (143.76 mm)
Width	0.98 in (24.89 mm)
Depth	4.05 in (102.87 mm)
Net Weight	2 lb(US) (0.91 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Product Certifications	cULus IEC
Ambient Air Temperature For Operation	104 °F (40 °C)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.81 in (4.6 cm)
Package 1 Width	6.18 in (15.7 cm)
Package 1 Length	10.39 in (26.4 cm)
Package 1 Weight	21.76 oz (616.9 g)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information