

# Product data sheet

Specifications

SQUARE D



Transformer, dry type, 225kVA, 3 phase, 208V delta primary, 208Y/120V secondary, 24D, 150C rise

EE225T211H

## Main

Product	Energy Efficient Transformer
Enclosure Code	24D
Enclosure Type	NEMA 2
Insulation Temperature	428 °F (220 °C)
Phase	3 phases
Primary Voltage	208 V delta
Power Rating	225 kVA
Secondary Voltage	208Y/120 V
Full Capacity Taps	3 5 % 1+ 2-
Temperature Rise	150 °C
Winding Material	Aluminium

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications