

Product data sheet

Specifications



Circuit breaker accessory,
PowerPacT J, earth leakage
module, 150 to 250A

ELM250JD

Main

Range Of Product	PowerPact
Product Or Component Type	Earth leakage add-on block
Circuit Breaker Type	JL JJ JD JG

Complementary

[In] Rated Current	150...250 A
Network Type	AC
[Ue] Rated Operational Voltage	240...600 V
Earth-Leakage Sensitivity	30 mA 3000 mA 1000 mA 300 mA 100 mA
Earth-Leakage Protection Time Delay	Instantaneous 500 ms
Local Signalling	Trip indicator
Electrical Connection To Mcb	Plug in
Tightening Torque	228.35 lbf.in (25.8 N.m) 0.04...0.29 in² (25...185 mm²) AWG 4...350 kcmil)

Environment

Product Certifications	UL CSA
------------------------	-----------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.40 in (16.256 cm)
Package 1 Width	5.30 in (13.462 cm)
Package 1 Length	10.60 in (26.924 cm)
Package 1 Weight	4.06 lb(US) (1.842 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information