Product data sheet

Specifications





gearbox straight teeth GBX, Lexium, 60mm, reduction 3:1, 10arc.min, 28N.m

GBX060003K

Main

Mann	
Range Compatibility	Lexium ILA Lexium 28 Lexium 62 ILM Lexium 62 Lexium 32 Lexium ILS Lexium 52 Lexium SD3
Product Or Component Type	Planetary gearbox
Gear Box Type	Straight teeth
Device Short Name	GBX
Product Compatibility	BMH 2.76 in (70 mm), 1 BMH 2.76 in (70 mm), 2 BMH 2.76 in (70 mm), 3 BSH 2.17 in (55 mm), 1 BSH 2.17 in (55 mm), 2 BSH 2.17 in (55 mm), 3 BSH 2.76 in (70 mm), 1 BSH 2.76 in (70 mm), 2 BSH 2.76 in (70 mm), 2 BSH 2.76 in (70 mm), 2 BSH 2.76 in (70 mm), 2 ILS 2.24 in (57 mm), 3 BCH2 2.36 in (60 mm), 1 BCH2 2.36 in (60 mm), 2 SH3 MH3 ILM
Gearbox External Diameter	2.36 in (60 mm)
Reduction Ratio	3:1

Complementary

Maximum Torsional Backlash	10 arc.min
Torsional Rigidity	2.3 N.m/arcmin
Housing Colour	Black
Housing Material	Black anodized aluminium
Shaft Material	C 45
Additional Information	Lubricated for life
Service Life In Hours	30000 h 100 rpm 86 °F (30 °C)
Mounting Position	Any position
Efficiency	96 %

Maximum Radial Force Fr	340 N 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 $^\circ\mathrm{C}$				
Maximum Axial Force Fa	450 N 100 rpm, during 30000 hour at 30°C				
Moment Of Inertia	0.135 kg.cm²				
Continuous Output Torque	247.82 lbf.in (28 N.m) 100 rpm 86 °F (30 °C)				
Maximum Output Torque	398.28 lbf.in (45 N.m) 100 rpm 86 °F (30 °C)				
Net Weight	1.98 lb(US) (0.9 kg)				
Input Diameter	0.55 in (14.0 mm)				

Environment

Noise Level	58 dB 1 m, no-load			
Ip Degree Of Protection	Shaft output IP54			
Ambient Temperature For Operation	-13194 °F (-2590 °C)			

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.68 in (6.800 cm)
Package 1 Width	2.68 in (6.800 cm)
Package 1 Length	5.12 in (13.000 cm)
Package 1 Weight	28.78 oz (816.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	10
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	18.81 lb(US) (8.533 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				

Product data sheet

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



(1) GBK adaptation kit

(2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination

Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
55	35	30	2.5	16	5	60	40 h7	14 h7	M5 x 8	52

Values in in.

a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
2.16	1.38	1.18	0.10	063	0.19	2.36	1.57 h7	0.55 h7	M5 x 0.31	2.05