Product data sheet

Specification





gearbox straight teeth GBX, Lexium, 60mm, reduction 8:1, 10arc.min, 18N.m

GBX060008K

Main

mam						
Range Compatibility	Lexium ILS					
	Lexium 62					
	Lexium SD3					
	Lexium ILA					
	Lexium 28					
	Lexium 52					
	Lexium 32					
	Lexium 62 ILM					
Product Or Component Type	Planetary gearbox					
Gear Box Type	Straight teeth					
Device Short Name	GBX					
Product Compatibility	BMH 2.76 in (70 mm), 1					
	BSH 2.17 in (55 mm), 1					
	BSH 2.17 in (55 mm), 2					
	BSH 2.17 in (55 mm), 3					
	BSH 2.76 in (70 mm), 1					
	BRS3					
	ILA 2.24 in (57 mm), 1					
	ILA 2.24 in (57 mm), 2					
	ILS 2.24 in (57 mm), 1					
	ILS 2.24 in (57 mm), 2					
	ILS 2.24 in (57 mm), 3					
	BCH2 2.36 in (60 mm), 1					
	BCH2 2.36 in (60 mm), 2					
	SH3					
	MH3					
	ILM					
Gearbox External Diameter	2.36 in (60 mm)					
Reduction Ratio	8:1					

Complementary

•						
Maximum Torsional Backlash	10 arc.min					
Torsional Rigidity	2.3 N.m/arcmin					
Housing Colour	Black					
Housing Material	Black anodized aluminium					
Shaft Material	C 45					
Additional Information	Lubricated for life					
Service Life In Hours	30000 h 100 rpm 86 °F (30 °C)					
Mounting Position	Any position					
Efficiency	96 %					
Maximum Radial Force Fr	340 N 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 $^{\circ}\text{C}$					
Maximum Axial Force Fa	450 N 100 rpm, during 30000 hour at 30°C					

Apr 26, 2024 Life Is On Schneider

Moment Of Inertia	0.065 kg.cm ²				
Continuous Output Torque	159.31 lbf.in (18 N.m) 100 rpm 86 °F (30 °C)				
Maximum Output Torque	256.67 lbf.in (29 N.m) 100 rpm 86 °F (30 °C)				
Net Weight	1.98 lb(US) (0.9 kg)				
Input Diameter	0.55 in (14.0 mm)				

Environment

Noise Level	58 dB 1 m, no-load				
Ip Degree Of Protection	Shaft output IP54				
Ambient Temperature For Operation	-13194 °F (-2590 °C)				

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.68 in (6.8 cm)
Package 1 Width	2.76 in (7.0 cm)
Package 1 Length	5.08 in (12.9 cm)
Package 1 Weight	29.03 oz (823.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	19.28 lb(US) (8.744 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
⊘	Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)					
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information					
Environmental Disclosure	Product Environmental Profile					
Circularity Profile	No need of specific recycling operations					

GBX060008K

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



- (1) GBK adaptation kit
- (2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination
- Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

a2	а3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
55	35	30	2.5	16	5	60	40 h7	14 h7	M5 x 8	52

Values in in.

a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5	
2.16	1.38	1.18	0.10	063	0.19	2.36	1.57 h7	0.55 h7	M5 x 0.31	2.05	