# **Product data sheet**

Specifications





# gearbox straight teeth GBX, Lexium, 60mm, reduction 12:1 , 12arc.min, 44N.m

GBX060012K

### Main

Mann	
Range Compatibility	Lexium ILE
	Lexium ILA
	Lexium ILS
	Lexium 62
	Lexium 32
	Lexium 62 ILM
	Lexium 28
	Lexium 52
	Lexium SD3
Product Or Component Type	Planetary gearbox
Gear Box Type	Straight teeth
Device Short Name	GBX
Product Compatibility	BMH 2.76 in (70 mm), 1
	BMH 2.76 in (70 mm), 2
	BSH 2.17 in (55 mm), 1
	BSH 2.17 in (55 mm), 2
	BSH 2.17 in (55 mm), 3
	BSH 2.76 in (70 mm), 1
	BSH 2.76 in (70 mm), 2
	BRS3
	ILE 2.60 in (66 mm), 1
	ILE 2.60 in (66 mm), 2
	ILA 2.24 in (57 mm), 1
	ILA 2.24 in (57 mm), 2
	ILS 2.24 in (57 mm), 1
	ILS 2.24 in (57 mm), 2
	ILS 2.24 in (57 mm), 3
	BCH2 2.36 in (60 mm), 1
	BCH2 2.36 in (60 mm), 2
	SH3
	MH3
	ILM
Gearbox External Diameter	2.36 in (60 mm)
Reduction Ratio	12:1

# Complementary

Maximum Torsional Backlash	12 arc.min
Torsional Rigidity	2.5 N.m/arcmin
Housing Colour	Black
Housing Material	Black anodized aluminium
Shaft Material	C 45
Additional Information	Lubricated for life
Service Life In Hours	30000 h 100 rpm 86 °F (30 °C)
Mounting Position	Any position

Efficiency	94 %					
Maximum Radial Force Fr	340 N 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 $^\circ\text{C}$					
Maximum Axial Force Fa	450 N 100 rpm, during 30000 hour at 30°C					
Moment Of Inertia	0.127 kg.cm <sup>2</sup>					
Continuous Output Torque	389.43 lbf.in (44 N.m) 100 rpm 86 °F (30 °C)					
Maximum Output Torque	619.55 lbf.in (70 N.m) 100 rpm 86 °F (30 °C)					
Net Weight	2.43 lb(US) (1.1 kg)					
Input Diameter	0.55 in (14.0 mm)					

### Environment

Noise Level	58 dB 1 m, no-load			
Ip Degree Of Protection	Shaft output IP54			
Ambient Temperature For Operation	-13194 °F (-2590 °C)			

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	2.76 in (7.0 cm)
Package 1 Length	5.71 in (14.5 cm)
Package 1 Weight	2.24 lb(US) (1.015 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	23.47 lb(US) (10.648 kg)

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


### **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				

## Product data sheet

#### **Dimensions Drawings**

#### **Dimensions with Servo Motor Adaptation Kit**



(1) GBK adaptation kit

(2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination

Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
67.5	35	30	2.5	16	5	60	40 h7	14 h7	M5 x 8	52

Values in in.

a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
2.66	1.38	1.18	0.10	063	0.19	2.36	1.57 h7	0.55 h7	M5 x 0.31	2.05