



# SWITCH FUSIBLE HD 600V 800A 3P NEMA1

H367

### Main

| Product                   | Single Throw Safety Switch  |
|---------------------------|---|
| Duty Rating               | Heavy duty  |
| Device Application        | Heavy application   |
| Disconnect Type           | Fusible disconnect  |
| Factory Installed Neutral | None  |
| Network Number Of Phases  | 3 phases  |
| Number Of Poles           | 3   |
| Current Rating            | 800 A   |
| Voltage Rating            | 600 V AC/DC   |
| Enclosure Rating          | NEMA 1 steel  |
| Motor Power Hp            | 200 hp at 480 V AC 5060 Hz for 3 phases motors<br>500 hp at 480 V AC 5060 Hz for 3 phases motors<br>250 hp at 600 V AC 5060 Hz for 3 phases motors<br>500 hp at 600 V AC 5060 Hz for 3 phases motors<br>50 hp at 600 V DC |

### Complementary

| Short-Circuit Current | 200 kA maximum for L   |
|-----------------------|--|
| Fuse Type             | L  |
| Mounting Type         | Surface  |
| Electrical Connection | Lugs   |
| Wiring Configuration  | 3-wire   |
| Wire Size             | AWG 3/0750 kcmil copper or aluminum                                  |
| Tightening Torque     | 375 lbf.in (42.37 N.m) 0.130.59 in² (85.01380 mm²) AWG 3/0750 kcmil) |
| Depth                 | 17.75 in (450.85 mm)   |
| Width                 | 36.62 in (930.15 mm)   |
| Height                | 69.13 in (1755.90 mm)  |
| Net Weight            | 369.94 lb(US) (167.8 kg)   |

### **Environment**

Certifications UL listed file E2875

## **Packing Units**

Unit Type Of Package 1 PCE

| Number Of Units In Package 1 | 1                          |
|------------------------------|----------------------------|
| Package 1 Height             | 73.82 in (187.5 cm)        |
| Package 1 Width              | 30.00 in (76.2 cm)         |
| Package 1 Length             | 37.99 in (96.5 cm)         |
| Package 1 Weight             | 358.00 lb(US) (162.386 kg) |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant with Exemptions   |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |

#### **Dimensions Drawings**

#### **Approximate Dimensions**

