



SWITCH NONFUSIBLE HD 600V 60A 3P NEMA7,9

H60XFA

Discontinued on: Nov 20, 2023

(!) Discontinued

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Fusible disconnect	
Factory Installed Neutral	None	
Network Number Of Phases	3 phases	
Number Of Poles	3	
Current Rating	60 A	
Voltage Rating	600 V AC 250 V DC	
Enclosure Rating	NEMA 7/9 cast aluminium	
Motor Power Hp	15 hp at 240 V AC 5060 Hz for 3 phases motors 30 hp at 480 V AC 5060 Hz for 3 phases motors 50 hp at 600 V AC 5060 Hz for 3 phases motors	

Complementary

Short-Circuit Current	10 kA	
Mounting Type	Surface	
Electrical Connection	Screw-clamp terminals	
Wire Size	AWG 14AWG 3 copper AWG 12AWG 3 aluminum	
Tightening Torque	50 lbf.in (5.65 N.m) AWG 3) 45 lbf.in (5.08 N.m) AWG 6AWG 4) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) AWG 8) 50 lbf.in (5.65 N.m) 0.000.01 in² (2.065.261 mm²) AWG 14AWG 10)	
Depth	6.96 in (176.78 mm)	
Width	9.87 in (250.70 mm)	
Height	15.93 in (404.62 mm)	
Net Weight	26.01 lb(US) (11.8 kg)	

Environment

Certifications UL listed file E2875
CSA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.40 in (18.796 cm)
Package 1 Width	10.20 in (25.908 cm)
Package 1 Length	17.10 in (43.434 cm)
Package 1 Weight	26.45 lb(US) (11.998 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations