

Product data sheet

Specifications

SQUARE D

Green Premium™



Box, I-Line Panelboard, HCP-SU,
28in W x 86in H x 13in D, Type
3R/12, w/trim

HC2886WP

Main

Range Of Product	I-Line
Product Or Component Type	Enclosure
Device Application	Panelboard
Device Short Name	HCP-SU

Complementary

[In] Rated Current	800 A
Enclosure Nominal Width	25.98 in (660 mm)
Enclosure Nominal Height	85.98 in (2184 mm)
Enclosure Nominal Depth	9.49 in (241 mm)
Net Weight	352.74 lb(US) (160 kg)
Height	86 in (2184.40 mm)
Depth	13 in (330.20 mm)

Environment

Nema Degree Of Protection	NEMA 3R/12
Standards	UL CSA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	87.01 in (221.0 cm)
Package 1 Width	27.99 in (71.1 cm)
Package 1 Length	14.02 in (35.6 cm)
Package 1 Weight	352.00 lb(US) (159.665 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Pvc Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations