



# Box, I-Line Panelboard, HCM, 32in W x 48in H x 8.25in D, Type 1

HC3248B

#### Main

Range Of Product	I-Line
Product Or Component Type	Enclosure
Device Application	Panelboard
Device Short Name	HCM

### Complementary

[In] Rated Current	600 A 400 A 800 A 225 A	
Enclosure Nominal Width	32.01 in (813 mm)	
Enclosure Nominal Height	47.99 in (1219 mm)	
<b>Enclosure Nominal Depth</b>	8.27 in (210 mm) 9.49 in (241 mm)	
Net Weight	77.34 lb(US) (35.08 kg)	
Height	48 in (1219.20 mm)	
<b>Depth</b> 8.25 in (209.55 mm)		

#### **Environment**

Nema Degree Of Protection	NEMA 1	
Standards	UL CSA	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.99 in (20.3 cm)
Package 1 Width	32.01 in (81.3 cm)
Package 1 Length	47.99 in (121.9 cm)
Package 1 Weight	77.33 lb(US) (35.076 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations