# Product data sheet

Specifications



# SWITCH NOT FUSIBLE HD 600V 200A 4P NEMA1

HU464

#### Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Network Number Of Phases	3 phases
Number Of Poles	4
Current Rating	200 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 1 steel
Motor Power Hp	50 hp at 240 V AC 5060 Hz for 2 phases motors 60 hp at 240 V AC 5060 Hz for 3 phases motors 50 hp at 480 V AC 5060 Hz for 2 phases motors 125 hp at 480 V AC 5060 Hz for 3 phases motors 50 hp at 600 V AC 5060 Hz for 2 phases motors 150 hp at 600 V AC 5060 Hz for 3 phases motors 40 hp at 250 V DC 50 hp at 600 V DC

## Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	4-wire
Wire Size	AWG 6250 kcmil copper or aluminum
Tightening Torque	275 lbf.in (31.07 N.m) 0.020.20 in <sup>2</sup> (13.3127 mm <sup>2</sup> ) AWG 6250 kcmil)
Depth	8.75 in (222.25 mm)
Width	24.88 in (631.95 mm)
Height	29 in (736.60 mm)
Net Weight	80.01 lb(US) (36.29 kg)

## Environment

Certifications

UL listed file E2875

## **Packing Units**

Unit Type Of Package 1

PCE

Number Of Units In Package 1	1
Package 1 Height	7.40 in (18.796 cm)
Package 1 Width	17.10 in (43.434 cm)
Package 1 Length	26.30 in (66.802 cm)
Package 1 Weight	43.50 lb(US) (19.731 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations