

Product data sheet

Specifications



Circuit breaker, Stab-Lok, 50A, 2 pole, 120/240VAC, 10kA, plug in mount

NC0250

Main

Range Of Product	Stab-lok
Product Or Component Type	Miniature circuit-breaker
[In] Rated Current	50 A
[Ue] Rated Operational Voltage	120/240 V AC
Poles Description	2P
Breaking Capacity	10 kA

Complementary

Mounting Mode	Plug-in
Electrical Connection	Screw connector
Awg Gauge	AWG 14...AWG 4 copper

Environment

Product Certifications	CSA
------------------------	-----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.50 in (8.89 cm)
Package 1 Weight	5.92 oz (167.829 g)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information