Product data sheet

Specification





Spacial CRN plain door w/o mount.plate. H400xW600xD250 IP66 IK10 RAL7035..

NSYCRN46250

Main

| Range | Spacial |
|-----------------------------|--|
| Product Name | Spacial CRN |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure Nominal Height | 15.75 in (400 mm) |
| Enclosure Nominal Width | 23.62 in (600 mm) |
| Enclosure Nominal Depth | 9.84 in (250 mm) |
| Installation Accessory Type | Wall-mounting |
| Device Composition | 1 body 1 cable gland plate 1 door 1 lock |
| Door Type | Plain |
| Mounting Plate Description | Without mounting plate |

Complementary

| Body Type | Sides made from a single folded section Back welded with double profile forming a protected sealed area |
|-----------------------------|--|
| Number Of Doors | Front face 1 |
| Door Opening Side | Reversible 120 °) |
| Lock Type | 3 mm double-bar lock |
| Type Of Gland Plate | Standard |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges Cable gland plate by screws |
| Material | Body steel |
| Surface Finish | epoxy-polyester powder |
| Colour | grey RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | cUL UL DNV-GL |
| Net Weight | 23.85 lb(US) (10.816 kg) |

Environment

| Ip Degree Of Protection | IP66 IEC 60529 |
|-------------------------|----------------|
| Ik Degree Of Protection | IK10 IEC 62262 |

Packing Units

| • | |
|------------------------------|----------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 10.43 in (26.500 cm) |
| Package 1 Width | 16.14 in (41.000 cm) |
| Package 1 Length | 24.21 in (61.500 cm) |
| Package 1 Weight | 23.06 lb(US) (10.459 kg) |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 27 |
| Package 2 Height | 86.61 in (220.000 cm) |
| Package 2 Width | 39.37 in (100.000 cm) |
| Package 2 Length | 47.24 in (120.000 cm) |
| Package 2 Weight | 651.23 lb(US) (295.393 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |