

# Product data sheet

Specifications



Spacial CRN plain door w/o  
mount.plate. H500xW400xD150  
IP66 IK10 RAL7035..

NSYCRN54150

## Main

Range	Spacial
Product Name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	19.69 in (500 mm)
Enclosure Nominal Width	15.75 in (400 mm)
Enclosure Nominal Depth	5.91 in (150 mm)
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 cable gland plate 1 door 1 lock
Door Type	Plain
Mounting Plate Description	Without mounting plate

## Complementary

Body Type	Back welded with double profile forming a protected sealed area Sides made from a single folded section
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Standard
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Body steel
Surface Finish	epoxy-polyester powder
Colour	grey RAL 7035)
Standards	IEC 62208
Product Certifications	cUL UL DNV-GL
Net Weight	16.40 lb(US) (7.438 kg)

## Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.89 in (17.500 cm)
Package 1 Width	16.14 in (41.000 cm)
Package 1 Length	20.08 in (51.000 cm)
Package 1 Weight	16.81 lb(US) (7.627 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	42
Package 2 Height	86.61 in (220.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	734.88 lb(US) (333.334 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations