Product data sheet

Specifications





Terminal block, Linergy TR, greenyellow, 35mm2, protective earth, 2 points, Set of 50

NSYTRV352PE

Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Terminal block
Device Short Name	TRV
Terminal Block Type	Protective earth
Terminal Block Level	1
Mounting Mode	Clip-on
Nominal Cross Section	0.05 in² (35 mm²)
Length	2.59 in (65.7 mm)
Colour	Green-yellow
Quantity Per Set	Set of 50

Complementary

,	
Width	0.63 in (16 mm)
Height	2.37 in (60.2 mm)
Connections - Terminals	1 x screw terminal upstream 1 x screw terminal downstream
Number Of Connections	2
Connection Position	Sideways
Number Of Measurement Input	2
Cable Cross Section	0.000.08 in² (1.550 mm²), solid 0.000.05 in² (2.535 mm²), flexible with cable end 0.000.08 in² (1.550 mm²), flexible without cable end
Tightening Torque	28.3232.75 lbf.in (3.23.7 N.m)
Wire Stripping Length	0.71 in (18 mm)
Tool Type	Connection screwdriver Disconnection screwdriver
[In] Rated Current	125 A EN/IEC 60947-7-1
Material	Polyamide 6/6: insulating case
Dielectric Loss	0.01 at 1 MHz IEC 60250 0.01 at 1 MHz VDE 0303-T4
Dielectric Constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m IEC 60093 10000 MΩ.m VDE 0303-T30

Surface Resistance	1000 GΩ IEC 60093
	1000 GΩ VDE 0303-T30
Creep Resistance	500 CTI (> 400 kB) IEC 60093
	500 CTI (> 400 kB) VDE 0303-T30
Flame Retardance	V0 0.03 in (0.8 mm) UL 94
Net Weight	3.03 oz (85.79 g)
Range Compatibility	Prisma G
	Prisma P
	Prisma PH Prisma Pack
	Spacial
	Kaedra
	Pragma
	TeSys
Product Compatibility	Spacial enclosures
Environment	
Product Certifications	VDE
	EAC
	CSA
	cURus IEC-Ex
	GL
	ATEX
Dielectric Strength	1000 V IEC 60243-1
Ambient Air Temperature For Operation	-40266 °F (-40130 °C) IEC 60216-1 -40266 °F (-40130 °C) VDE 0304-T21
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.500 cm)
Package 1 Width	7.09 in (18.000 cm)
Package 1 Length	11.02 in (28.000 cm)
Package 1 Weight	3.00 oz (85.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	3.74 in (9.500 cm)
Package 2 Width	7.09 in (18.000 cm)
Package 2 Length	11.02 in (28.000 cm)
Package 2 Weight	9.74 lb(US) (4.418 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	1700

Contractual warranty

Package 3 Height

Package 3 Width

Package 3 Length

Package 3 Weight

29.53 in (75.000 cm)

23.62 in (60.000 cm)

31.50 in (80.000 cm)

356.22 lb(US) (161.580 kg)

Warranty

18 months

Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations