





Elbow, Powerbus busway, left, 100A, 600V, 3 phase, 4 wire, 4A config

PBCF4A100ALLB

! Discontinued on: Oct 9, 2023

! Discontinued

Main

Product Or Component Type	Elbow
Range Of Product	Powerbus

Complementary

Current Rating	100 A
Busbar Configuration	4A L1 + L2 + N + L3
Busbar Material	Silver plated copper: busbar
Integral Ground	50 percent capacity integral ground bus
Voltage Rating	600 V AC
Number Of Phases	3 phases
Wiring Configuration	4-wire (100 percent neutral)
Enclosure Material	Painted aluminium black
Installation Direction	Left

Environment

Ip Degree Of Protection IP40

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	13 00 lb(US) /5 897 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information