

# Product data sheet

Specifications

SQUARE D

Green Premium™



Circuit breaker, PowerPacT Q, 80A, 2 pole, 240VAC, 25kA, lugs, thermal magnetic, 80%

QDL22080

## Main

Range	PowerPact
Product Name	PowerPact Q
Product Or Component Type	Circuit breaker
Device Application	Distribution

## Complementary

[In] Rated Current	80 A
Number Of Poles	2P
Control Type	Operating handle
Breaking Capacity Code	D
Breaking Capacity	25 kA 120/208 V AC 50/60 Hz UL 25 kA 240 V AC 50/60 Hz UL
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz UL
Network Frequency	50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV UL
Trip Unit Technology	Thermal-magnetic
Magnetic Tripping Current	1800 A
Magnetic Hold Current	1000 A
Continuous Current Rating	80 %
Utilisation Category	Category A
Mechanical Durability	1000 cycles loaded 5000 cycles no load
Local Signalling	1 trip indicator green)
Mounting Mode	Unit mount lug)
Mounting Support	Lug
Electrical Connection	Lugs, load Lugs, line
Tightening Torque	247.82 lbf.in (28 N.m) 0.04...0.23 in <sup>2</sup> (25...150 mm <sup>2</sup> ) AWG 4...300 kcmil)
Power Wire Stripping Length	0.87 in (22 mm)
Height	6.47 in (164.34 mm)
Width	3 in (76.20 mm)
Depth	3.93 in (99.82 mm)

---

Circuit Breaker Application	HACR rated
-----------------------------	------------

## Environment

---

Standards	UL CSA NEMA NOM-003-SCFI-2000
-----------	--

---

Product Certifications	UL CSA NOM
------------------------	------------------

---

Ambient Air Temperature For Operation	104...158 °F (40...70 °C)
---------------------------------------	---------------------------

---

## Packing Units

---

Unit Type Of Package 1	PCE
------------------------	-----

---

Number Of Units In Package 1	1
------------------------------	---

---

Package 1 Height	5.56 in (14.127 cm)
------------------	---------------------

---

Package 1 Width	5.81 in (14.757 cm)
-----------------	---------------------

---

Package 1 Length	9.75 in (24.765 cm)
------------------	---------------------

---

Package 1 Weight	3.32 lb(US) (1.505 kg)
------------------	------------------------

---

## Contractual warranty

---

Warranty	18 months
----------	-----------

---

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Reach Free Of Svhc

---

Mercury Free

---

Rohs Exemption Information [Yes](#)

---

Pvc Free

---

Halogen Free Product

---

## Certifications & Standards

**Eu Rohs Directive** [Compliant](#)  
[EU RoHS Declaration](#)

---

**China Rohs Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

---

**Environmental Disclosure** [Product Environmental Profile](#)

---