



# Mini circuit breaker, QO, 20A, 3 pole, 120/240VAC, 10kA, bolt on

QOB320

#### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate

# Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 240 V AC 10 kA 120 V AC
Number Of Panel Spaces	3
Wire Size	AWG 14AWG 8 copper or aluminum
Tightening Torque	35.40 lbf.in (4 N.m)
Height	2.99 in (76 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	0.80 lb(US) (0.363 kg)

#### **Environment**

Certifications	UL listed CSA	
Ambient Rating	104 °F (40 °C)	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.30 in (8.382 cm)
Package 1 Width	2.30 in (5.842 cm)

Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	12.80 oz (363.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	3.60 in (9.144 cm)
Package 2 Width	2.30 in (5.842 cm)
Package 2 Length	7.10 in (18.034 cm)
Package 2 Weight	2.55 lb(US) (1.157 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	36
Package 3 Height	3.90 in (9.906 cm)
Package 3 Width	14.60 in (37.084 cm)
Package 3 Length	21.70 in (55.118 cm)
Package 3 Weight	30.98 lb(US) (14.052 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

## **Certifications & Standards**

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration