

Product data sheet

Specifications



Surge protection device,
Surgebreaker Plus, 120/240VAC, 80
kA, 1 phase, 3 wire, combination
cover, consumer pack

SDSB80111CCP

Main

Accessory / Separate Part Category	Protection accessory
Electrical Circuit Type	Coaxial Telephone AC
Product Or Component Type	Surge suppressor
Range Of Product	QO
Type Of Packing	Consumer packaging

Complementary

[Ue] Rated Operational Voltage	120/240 V AC
Range Compatibility	Surgebreaker Plus
Device Mounting	Surface Flush
Network Number Of Phases	1 phase
Number Of Circuits	3
Number Of Spaces	30
Mounting Location	Service entrance
Wiring Configuration	3-wire

Environment

Nema Degree Of Protection	NEMA 1
Product Certifications	UL cULus CSA
Standards	UL 1449 ANSI/IEEE C62.41 CSA C22.2 No 8

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.30 in (13.462 cm)
Package 1 Width	7.30 in (18.542 cm)
Package 1 Length	18.00 in (45.72 cm)
Package 1 Weight	7.21 lb(US) (3.27 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
-------------------	---------------------
