Product data sheet

Specifications





USB configurable monolithic tower light, Harmony XVGU, multi color programmable lights 60mm, steady/flashing LED buzzer

XVGU3SWV

() Discontinued

Main

Range Of Product	Harmony XVGU
Product Or Component Type	USB configurable monolithic tower light
Beacon Or Indicator Bank Unit Type	3 illuminated units
Sound Signalling	Buzzer
Mounting Diameter	2.36 in (60 mm)
Component Name	XVGU
Light Source	LED steady or flashing multi-colour
Indicator Bank Base Type	Base with integrated buzzer
Noise Level	82 dB 2 tone buzzer)1 m

Complementary

Material	PC: globe
Device Mounting	Direct mounting
Light Block Color	Clear/clear
[Us] Rated Supply Voltage	5 V DC
Connector Type	USB type A female
Current Consumption	400 mA
Sound Frequency	2700 Hz 3800 Hz
Power Consumption In W	2 W
Flashing Frequency	2 Hz flashing LED unit 1 Hz flashing LED unit
Product Compatibility	Vijeo Designer 4.6 indoor use only HMIGTO XBTGT XBTGK XBTGC1. XBTGC2. XBTGH
Net Weight	0.66 lb(US) (0.3 kg)

Environment

Standards

IEC 61000-6-2 IEC 61000-6-4

Product Certifications	GOST cUL CE RCM UL 508
Ambient Air Temperature For Storage	-31158 °F (-3570 °C)
Ambient Air Temperature For Operation	32131 °F (055 °C)
Electrical Shock Protection Class	Class I
Ip Degree Of Protection	IP54

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.11 in (7.9 cm)
Package 1 Width	3.11 in (7.9 cm)
Package 1 Length	12.24 in (31.1 cm)
Package 1 Weight	12.35 oz (350.0 g)
Unit Type Of Package 2	S04
Number Of Units In Package 2	21
Package 2 Height	11.81 in (30 cm)
Package 2 Width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Package 2 Weight	18.96 lb(US) (8.6 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	84
Package 3 Height	31.50 in (80 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	94.60 lb(US) (42.908 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards


Circularity Profile	No need of specific recycling operations
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

Product data sheet

Dimensions Drawings


Dimensions

Direct Base Mounting




Mounting and Clearance

Mounting on Horizontal Support for Direct Base Mounting



- (1) Cable outlet
- (2) Buzzer opening position
- (3) Waterproof rubber seal
- (4) Hexagon nut with flange



Choose a flat surface with enough strength and with little vibration for installation.Mount this product according to the figure to maintain IP characteristics

- (1) OK
- (2) NO