



LED pilot light with black bezel, Harmony XVL, Ø 8, IP40, red, protruding included, 5 V, faston

XVLA114

Discontinued on: Jun 15, 2023



Main

Range Of Product	Harmony XVL			
Product Or Component Type	LED pilot light with black bezel			
Component Name	XVL			
Mounting Diameter	0.31 in (8 mm)			
Light Source	Protruding LED			
Light Block Colour	Red			
Protection Type	Built-in by diode Integral ballast resistor			
[Us] Rated Supply Voltage	5 V			
Ip Degree Of Protection	IP40 IEC 60529 IP40 NF C 20-010			

Complementary

Supply Circuit Type	DC
Connections - Terminals	Tag for Faston connectors 2.8 x 0.5 mm Tag for soldering connectors
Current Consumption	25 mA
[Ui] Rated Insulation Voltage	50 V IEC 60947-1
Bulb Lifespan	100000 h
Nominal Voltage Limit	0.81.1 Un
Terminals Description Iso N°1	(X1-X2)PL
Height	0.47 in (12 mm)
Width	0.47 in (12 mm)
Depth	1.34 in (34 mm)
Net Weight	0.01 lb(US) (0.003 kg)

Environment

Product Certifications	CSA UL
Protective Treatment	TC
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)

Overvoltage Category	Class 3 IEC 60536
	Class 3 NF C 20-030

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.47 in (1.2 cm)
Package 1 Width	0.47 in (1.2 cm)
Package 1 Length	1.38 in (3.5 cm)
Package 1 Weight	0.11 oz (3.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.18 in (3.0 cm)
Package 2 Width	4.33 in (11.0 cm)
Package 2 Length	4.33 in (11.0 cm)
Package 2 Weight	1.06 oz (30.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	17.99 oz (510.0 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins			
Circularity Profile	No need of specific recycling operations			

Dimensions Drawings

LED Pilot Light

Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.


С		Ø	
mm	in.	mm in.	
32	1.26	12	0.47

XVLA114

Mounting and Clearance

LED Pilot Light

Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
8.2	0.32	12.5	0.49	12.5	0.49

Apr 25, 2024