Product data sheet

Specifications





LED pilot light with black bezel, Harmony XVL, red, 8mm, IP40, protruding LED, faston connectors, 12V

XVLA124

Main

Range Of Product	Harmony XVL
Product Or Component Type	LED pilot light with black bezel
Component Name	XVL
Mounting Diameter	0.31 in (8 mm)
Light Source	Protruding LED
Light Block Colour	Red
Protection Type	Built-in by diode Integral ballast resistor
[Us] Rated Supply Voltage	12 V
Ip Degree Of Protection	IP40 IEC 60529 IP40 NF C 20-010

Complementary

Supply Circuit Type	DC		
Connections - Terminals	Tag for Faston connectors 2.8 x 0.5 mm Tag for soldering connectors		
Current Consumption	18 mA		
[Ui] Rated Insulation Voltage	50 V IEC 60947-1		
Bulb Lifespan	100000 h		
Nominal Voltage Limit	0.81.1 Un		
Terminals Description Iso N°1	(X1-X2)PL		
Height	0.47 in (12 mm)		
Width	0.47 in (12 mm)		
Depth	1.34 in (34 mm)		
Net Weight	0.01 lb(US) (0.003 kg)		

Environment

Product Certifications	UL CSA
Protective Treatment	TC
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Overvoltage Category	Class 3 IEC 60536 Class 3 NF C 20-030

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (1.0 cm)
Package 1 Width	0.39 in (1.0 cm)
Package 1 Length	1.57 in (4.0 cm)
Package 1 Weight	0.11 oz (3.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.18 in (3.0 cm)
Package 2 Width	5.12 in (13.0 cm)
Package 2 Length	5.12 in (13.0 cm)
Package 2 Weight	1.09 oz (31.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	18.77 oz (532.0 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards


Circularity Profile	No need of specific recycling operations		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Environmental Disclosure	Product Environmental Profile		
China Rohs Regulation	China RoHS declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
Reach Regulation	REACh Declaration		

Product data sheet

Dimensions Drawings

LED Pilot Light

Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.

С		Ø	
mm	in.	n. mm in.	
32	1.26	12	0.47

Product data sheet

Mounting and Clearance

LED Pilot Light

Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
8.2	0.32	12.5	0.49	12.5	0.49