# Product data sheet

Specifications





## LED pilot light with black bezel, Harmony XVL, yellow, 8mm, IP40, protruding LED, faston connectors, 12V

XVLA125

### Main

in an i	
Range Of Product	Harmony XVL
Product Or Component Type	LED pilot light with black bezel
Component Name	XVL
Mounting Diameter	0.31 in (8 mm)
Light Source	Protruding LED
Light Block Colour	Yellow
Protection Type	Integral ballast resistor Built-in by diode
[Us] Rated Supply Voltage	12 V
Ip Degree Of Protection	IP40 IEC 60529 IP40 NF C 20-010

### Complementary

· · · · · · · · · · · · · · · · · · ·			
Supply Circuit Type	DC		
Connections - Terminals	Tag for Faston connectors 2.8 x 0.5 mm Tag for soldering connectors		
Current Consumption	18 mA		
[Ui] Rated Insulation Voltage	50 V IEC 60947-1		
Bulb Lifespan	100000 h		
Nominal Voltage Limit	0.81.1 Un		
Terminals Description Iso N°1	(X1-X2)PL		
Height	0.47 in (12 mm)		
Width	0.47 in (12 mm)		
Depth	1.34 in (34 mm)		
Net Weight	0.01 lb(US) (0.003 kg)		

### Environment

Product Certifications	UL CSA
Protective Treatment	TC
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Overvoltage Category	Class 3 IEC 60536 Class 3 NF C 20-030

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	2.36 in (6.0 cm)
Package 1 Weight	0.11 oz (3.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	0.98 in (2.5 cm)
Package 2 Width	4.72 in (12.0 cm)
Package 2 Length	4.72 in (12.0 cm)
Package 2 Weight	1.16 oz (33.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	16.75 oz (475.0 g)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**


Circularity Profile	No need of specific recycling operations		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Environmental Disclosure	Product Environmental Profile		
China Rohs Regulation	China RoHS declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
Reach Regulation	REACh Declaration		

## Product data sheet

#### **Dimensions Drawings**

#### LED Pilot Light

#### Dimensions



- (1) Tags for Faston connectors or soldered connections
- e panel thickness: 1 to 8 mm/0.03 to 0.31 in.

С		Ø	
mm in.		mm	in.
32	1.26	12	0.47

## Product data sheet

Mounting and Clearance

#### LED Pilot Light

#### Panel Drilling



Ø min		G min		H min	
mm	in.	mm	in.	mm	in.
8.2	0.32	12.5	0.49	12.5	0.49