

Fiche Produit

Spécifications

SQUARE 



Non-Reversing Starter Size 00, 3-Pole, Motor Logic SSOLR (Class 20)

8536SAG12V02CH20P1SX20

Principal

Type De Produit	Starter
Gamme De Produit	S
Starter Type	Non réversible

Complémentaire

Nema Size	00
Courant Nominal	9 A
Nombre De Pôles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phases
Type Of Overload	État solide Motor Logic classe 20
Horsepower Rating	1.5 HPà 200 V AC 1.5 HPà 230 V AC 2 HPà 460 V AC 2 HPà 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator marche incandescent
Auxiliary Contacts	2F
Terminal Type	Borniers à vis-étrier

Environnement

Enclosure Type	NEMA 1 feuille d'acier peint
Certifications	CSA listé UL NEMA

Garantie contractuelle

Garantie	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications