



Main

Product or component type	Circuit breaker
Range of product	PowerPact M
Breaking capacity code	G
Trip unit technology	Electronic basic ET 1.0 LI

Complementary

Current sensor rating range	500 A
[In] rated current	500 A
[Ue] rated operational voltage	600 V AC
Mounting mode	Unit mount
Poles description	3P
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
Continuous current rating	80 %
Electrical connection	Lugs load Lugs line
AWG gauge	AWG 3/0...500 kcmil aluminium/copper 3(cables(s))

Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------