



### Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	Compact : fixed INS250 source changeover - control: mechanical interlock - vertical installation Compact : fixed INV250 source changeover - control: mechanical interlock - vertical installation Compact : fixed INS250 source changeover - control: direct front rotary handle - vertical installation Source changeover : fixed NSX100...250 source changeover - control: mechanical interlock - vertical installation
Poles description	2 x 3P : fixed : NSX100...250 source changeover vertical installation 2 x 3P : fixed : INS250 source changeover vertical installation 2 x 3P : fixed : INV250 source changeover vertical installation 2 x 4P : fixed : NSX100...250 source changeover vertical installation 2 x 4P : fixed : INS250 source changeover vertical installation 2 x 4P : fixed : INV250 source changeover vertical installation

### Complementary

Installation description	Cubicle - width 650 mm, depth 400 mm
Number of vertical modules [50 mm]	9 module(s) : INS250 source changeover, direct in 650 mm Wide cubicle 9 module(s) : INV250 source changeover, direct in 650 mm Wide cubicle 10 module(s) : NSX100...250 source changeover, direct in 650 mm Wide cubicle
Height	289 mm
Width	536 mm
Product weight	3.3 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

Standards	IEC 61439-2
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Toote keskkonnaprofiil</a>
Product end of life instructions	Available <a href="#">Kasutuselt kõrvaldamise teave</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------