



Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	Source changeover: fixed NSX400...630 source changeover without earth leakage protection - control: direct front rotary handle - horizontal installation Compact : fixed INS320...630 source changeover - control: direct front rotary handle - horizontal installation Compact : fixed INV320...630 source changeover - control: direct front rotary handle - horizontal installation
Poles description	2 x 3P : fixed : NSX400...630 source changeover horizontal installation 2 x 4P : fixed : NSX400...630 source changeover horizontal installation 2 x 3P : fixed : INS320...630 source changeover horizontal installation 2 x 4P : fixed : INS320...630 source changeover horizontal installation 2 x 3P : fixed : INV320...630 source changeover horizontal installation 2 x 4P : fixed : INV320...630 source changeover horizontal installation

Complementary

Installation description	Cubicle - width 650 mm, depth 400 mm
Number of vertical modules [50 mm]	10 module(s) : NSX400...630 source changeover without earth leakage protection , direct in 650 mm Wide cubicle 10 module(s) : INS320...630 source changeover, direct in 650 mm Wide cubicle 10 module(s) : INV320...630 source changeover, direct in 650 mm Wide cubicle
Height	450 mm
Width	386 mm
Product weight	4.56 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

Standards	IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Toote keskkonnaprofiil
Product end of life instructions	Available Kasutuselt kõrvaldamise teave

Contractual warranty

Warranty period	18 months
-----------------	-----------