



### Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Compact: fixed INS630b...1600 - control: direct front rotary handle - vertical installation Compact: fixed INV630b...1600 - control: direct front rotary handle - vertical installation
Poles description	1 x 4P : mounting plate support : INS630b...1600 vertical installation 1 x 4P : mounting plate support : INV630b...1600 vertical installation
Operating position	Vertical

### Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm, depth 400 mm
Connection position	Rear connection Front connection
Number of vertical modules [50 mm]	6
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	300 mm
Width	500 mm
Product weight	0.92 kg
Material	Steel
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Toote keskkonnaprofiil</a>
Product end of life instructions	Available <a href="#">Kasutuselt kõrvaldamise teave</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------