



### Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Compact : fixed NS1600b - control: toggle - vertical installation Compact : fixed NS2000...3200 - control: toggle - vertical installation
Poles description	1 x 3P : mounting plate support : NS1600b vertical installation 1 x 4P : mounting plate support : NS1600b vertical installation 1 x 3P : mounting plate support : NS2000...3200 vertical installation 1 x 4P : mounting plate support : NS2000...3200 vertical installation
Operating position	Horizontal

### Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm, depth 400 mm Cubicle - width 650 mm, depth 600 mm
Connection position	Front connection
Number of vertical modules [50 mm]	8
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	400 mm
Width	500 mm
Product weight	1.02 kg
Material	Steel
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Toote keskkonnaprofiil</a>
Product end of life instructions	Available <a href="#">Kasutuselt kõrvaldamise teave</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------