



Main

Range of product	NS1600b...3200 NS630b...1600
Product or component type	Control unit
Range compatibility	Compact NS1600b...3200 Compact NS630b...1600
Device application	Distribution
Poles description	3P 4P
Protected poles description	3t 3t + N/2 4t
Network type	AC
Network frequency	50/60 Hz
Trip unit name	Micrologic 5.0
Trip unit technology	Electronic
Trip unit protection functions	Selective protection
Trip unit rating	630 A (50 °C) 800 A (50 °C) 1000 A (50 °C) 1250 A (50 °C) 1600 A (50 °C) 2000 A (50 °C) 3200 A (50 °C) 2500 A (50 °C)
Protection type	Instantaneous short-circuit protection Overload protection (long time) Short time short-circuit protection

Complementary

Mounting mode	Drawout Fixed
Long time pick-up adjustment type Ir	Adjustable
Long time pick-up adjustment range	0.4...1 x In
Long time delay adjustment type	Adjustable 9 settings
[Tr] long-time delay adjustment range	0.7...16.6 s 7.2 x Ir 0.7...24 s 6 x Ir

	12.5...600 s 1.5 x I _r
Thermal memory	20 mn
Short-time pick-up adjustment type I _{sd}	Adjustable 9 settings
[I _{sd}] short-time pick-up adjustment range	1.5...10 x I _r
Short-time delay adjustment type	Adjustable 5 settings
[T _{sd}] short-time delay adjustment range	0.02...0.5 s
Instantaneous pick-up adjustment type I _i	Adjustable
Instantaneous pick-up adjustment range	2...15 x I _n Off

Contractual warranty

Warranty period	18 months
-----------------	-----------